
# KN Crowder

# **SDL Louver Finishes**

# Colour Options & Re-coating Instructions

KN Crowder's SDL Louver series are finished using a VOC-free electrostatic painting process, which attracts paint evenly to all exposed metal surfaces. This ensures a uniform, continuous coating — inside and out — for enhanced protection against moisture and dust, resulting in a longer product lifespan.



### Stock Finish

Mineral Bronze is the standard in-stock finish.

### Other Finishes

Additional finishes, shown above, are available upon request.

Please contact Customer Service at customerservice@kncrowder.com for current lead times and pricing.

# Re-coating Instructions (Steel & Galvannealed Louvers only)

Powder-coated SDL Louvers made from steel or galvannealed steel may be re-coated in the field by following these steps:

#### Step #1: Abrasive Prep

Lightly abrade the entire surface with a non-shredding, non-rusting, non-splintering abrasive pad.

#### Step #2: Surface Cleaning

Thoroughly clean all parts before painting. After abrading, wipe down the surface with an alcohol-based cleaner to remove residue and reopen the surface for optimal paint adhesion. Always follow the cleaner manufacturer's instructions.

#### Step #3: Re-coating

Apply a high-quality paint suitable for metal.

Note: KN Crowder cannot guarantee the performance of any specific paint brand.